SINGLE USE MASK WITH FFP2D SL VALVE

Ref. 23276





TECHNICAL SHEET

MEASUREMENTS

Mask (mm)	136 x 129 x 54 (L x W x h)
Nose pad (mm)	110 x 28 x 1.5 (L x W x T)
Headband (mm)	700 x 4.5 x 1.0 (L x W x T)
Headband buckle (mm)	42 x 12 x 2.0 (L x W x T)
Valve (mm)	41 x 12 (D x h)

GENERAL DESCRIPTION AND MATERIALS

- Single use valved mask FFP2D SL
- Outer layer in polyester
- Inner layers in soft polypropylene
- Filter Media in electrostatic High Filtration Efficiency Melt-Brown (polypropylen)
- Headband in latex-free braided synthetic rubber with buckle in polypropylene
- Nosepad: polyethylene foam
- Polypropylene valve housing and synthetic rubber valve membrane

SPECIFICAL ADVANTAGES

- Allergic test
- No metallic pieces

- Pass the optional Dolomite Clogging test for more **comfortable breathing**
- Exhalation valve

MAIN APPLICATION FIELDS

- Protection against low toxicity solid and luiquid aerosols in concentrations up to 12x0EL
- Textile industry, craft industry, metallurgical industry, mining industry, underground civil engineering, woodwork, welding, melting, metal cutting out, hospitals, laboratories, medical controls
- Against calcium carbonate, china clay, cement, cellulose, sulfur, cotton, flour, carbon, ferrous metals, hardwood, glass fibers, plastic, vegetable oils and mineral oils, quartz, copper, aluminium, bacteria, fungi and mycobacterium tuberculosis (T.B.),
- Do not use in a place where oxygen concentration is less thand 17 % Vol.

PACKAGING

10 masks in a box

• 120 masks in a carton

STANDARDIZATION

This mask is in conformity with the model of individual safety equipment which correspond to

The CE Type-examination certificate 59765

Delivered by **BSI** (notified body n° 0086)

This mask is in conformity with the « **French JO notice** » 135 from 06/12/04.

EN 149 : 2001

SACLA – Z.I. de Rosarge – 01700 LES ECHETS – MIRIBEL – FRANCE Tèl. : (33) 04 72 26 57 57 – Fax. : (33) 04 72 26 51 70